



Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'FC12SCMP5Y'

Your search criteria matched only one product, shown below

FC12SCMP5Y



- Compatible with *Opticom*® and *Opticom*® HD Enclosures, Trays, Drawers and Patch Panels
 - Low insertion loss of 1.0dB typical; 1.5dB max. per cassette; ensures system meets IEEE 802.3ae max. channel loss specification of <2.6dB
 - Significantly reduce installation time and labor by eliminating field connector terminations
 - Factory terminated, assembled and 100% tested
 - Insertion loss and return loss data provided on every fiber cassette
 - Lifetime traceability of test data to a Q.C. number on each fiber cassette
- *MTP is a registered trademark of US Conec Ltd.

QuickNet™ MTP* Cassettes cannot be used in an angled patch panel

▪ Part Number	FC12SCMP5Y
▪ RoHS Compliancy Status	Compliant
▪ Note	FC12SCMP5Y replaces FC12SCMP5
▪ Part Description	OM1 62.5/125µm six SC duplex adapters to 5 meter pigtail; 12-fiber pre-terminated pigtail cassette.
▪ Product Type	Pre-Terminated Cassettes
▪ Fiber Compatibility	50/125µm
▪ Fiber Type	Multi
▪ CE Compliant	No
▪ Connection Type	SC
▪ Connector 1 Type	SC
▪ Connector 2 Type	Pigtail
▪ No. of Fibers	12
▪ Pigtail or MPO	Pigtail
▪ Pricing Description	12-Fiber Cassette w/6 Dupl S Connectors mm w/12 SC Pigtail
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.