

Search Results

Evaluate

- FAQ's
- Technical Papers
- DOCMTechnical Da..
- PDFTechnical Da..

Design a Solution


- Part Drawings
- PDFC240X240A*T ..
- Specification Sheets
- PDFRaised Panel..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'C240X240A8T-30'

Your search criteria matched only one product, shown below

C240X240A8T30



- Raised thermal transfer printable surface with high -tack adhesive for strong holding power
- Variety of sizes and colors for a wide range of applications
- Thermal transfer print technology provides crisp, clear, and durable text
- Use with Panduit thermal transfer resin ribbons

Part Number	C240X240A8T-30
RoHS Compliancy Status	Compliant
Part Description	Yellow, raised panel push button label.
Color	Yellow
Height (In.)	2.40
Height (mm)	60.9
Width (In.)	2.40
Width (mm)	60.9
Hole Diameter (In.)	1.18
Hole Diameter (mm)	30.0
Pricing Description	Raised Panel Label, Keyhole, 2.4"W x 2.4"H (61.0mm x 61.0mm), Yellow
Print-On Area Height (In.)	0.90
Print-On Area Height (mm)	22.9
Min. Order UOM	PC
Min. Order Qty.	500
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.