

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'CD-800-14'

Your search criteria matched only one product, shown below

CD-800-14



All tooling information, including crimp shut height dimension, is included on the product reel label.

Part Number	CD-800-14
RoHS Compliancy Status	RoHS directive is not applicable
Part Description	Die for CA-800 Applicator
60/40 Solder Slug Dia. (In.)	.125
60/40 Solder Slug Dia. (mm)	3.18
CE Compliant	No
CE Marking	No
Panduit Color Code	Red / Blue
Pricing Description	Die Insert, for use with CA-800 applicator, to terminate PANDUIT reeled disconnects
Wire Insulation Strain Relief	Metal Insulation Crimp
Wire Range	22 – 18 / 16 – 14
Wire Range (mm ²)	0.5 – 1.0 / 1.5 – 2.5
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.