



Search Results

- Evaluate
 - FAQ's
 - Press Releases
 - TG Terminati ..
 - Termination ..
 - Product Bulletins
 - PDFPANDUIT TG T ..
- Design a Solution
 - Part Drawings
 - PDFMiniCom TX6 ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
 - Installation Instructions
 - PDFTX6 PLUS and ..

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'CJ688TGOR-24'

Your search criteria matched only one product, shown below

CJ688TGOR-24



- Exceeds TIA/EIA-568-B.2-1 Category 6 and ISO 11801 2nd Edition Class E standards
- Each jack is 100% tested to ensure NEXT and RL performance and is individually serialized for traceability
- Utilizes patent-pending enhanced *Giga-TX*TM Technology for jack terminations which optimizes performance by maintaining cable pair geometry and eliminating conductor untwist
- Contacts plated with 50 microinches of gold for superior performance
- No punchdown tool required; termination tool (EGJT) ensures conductors are fully terminated by utilizing a smooth forward motion without impact on critical internal components for maximum reliability
- Optional termination tool (TGJT) reduces termination time by 25%, ideal for high volume installations
- Can be re-terminated a minimum of twenty times
- Off white termination cap designates Category 6 *PLUS* performance and provides positive strain relief; helps control cable bend radius and securely retains wires

- Terminates 4 -pair, 22 – 26 AWG, 100 ohm, solid or stranded twisted pair cable
- Termination cap is color coded for T568A and T568B wiring schemes
- Accepts 6 and 8-position modular plugs without damage
- Can be clearly identified with optional labels and icons
- Compatible with *Mini-Com*[®] Modular Patch Panels, Faceplates, and Surface Mount Boxes

To ensure optimal performance, *PANDUIT* recommends use with other *PANDUIT*[®] Category 6 *PLUS* components.

Part Number	CJ688TGOR24
RoHS Compliancy Status	Compliant
Part Description	Category 6, RJ45, 8position, 8-wire universal module, bulk packaged.
Product Type	Copper Jack Module
Color	Orange
No. of Module Spaces	1
Performance Level	Category 6
Pricing Description	Mini-Com Module, Cat 6, UTP, 8 pos 8 wire, Universal, Orange, TG Style, 24 Pk
Wiring Scheme	T568A/T568B
Min. Order UOM	PC
Min. Order Qty.	24
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.