

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFDMV1-63P-LY
 - Part Drawings
 - PDFMetric Piggy..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'DMV2-63P-L'

Your search criteria matched only one product, shown below

DMV2-63P-L



- Combination of female disconnect and male tab allows versatility in points of connection
- Multiple connection points allow additional circuits to be added to existing equipment without expensive rework
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- Maximum insulation temperature 194°F (90°C)
- Rated up to 600 V

| | |
|-------------------------------|---|
| Part Number | DMV2-63P-L |
| RoHS Compliancy Status | Compliant |
| Note | DMV2-63P-L replaces DMV2-63P-C |
| Part Description | Metric Piggyback Disconnect, vinyl barrel insulated, 1.5- 2.5mm ² wire range, 6.3 x .8mm tab size, vinyl barrel insulated. |
| Product Type | Disconnects - Metric |
| Length (mm) | 22.4 |
| Width (mm) | 7.4 |
| CE Compliant | No |
| Insulation | Vinyl |
| Max. Ins. (mm) | 4.06 |
| Panduit Color Code | Blue |
| Plating Type | Tinned |
| Pricing Description | Metric Piggyback Disconnect, vinyl barrel insulated, 1.5- 2.5mm ² wire range, 6.3 x .8mm tab size, vinyl barrel insulated. |
| Tab Size (mm) | 6.3 x 0.8 |
| Temperature Rating | 194 Degrees Fahrenheit (90 Degrees Celsius) |
| Tool | CT-1551 |
| Wire Range (mm ²) | 1.5 – 2.5 |
| Min. Order UOM | PC |
| Min. Order Qty. | 50 |
| BOM Qty. (# of Pkgs.) | <input type="text" value="0"/> |
| Add to Favorite Product List |  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.