

Search Results

- Evaluate
 - FAQ's
 - Selection Guides
 - PDFConvenience..
- Design a Solution
 - Part Drawings
 - PDFFemale Disco..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'DNF18-110FIB-E'

Your search criteria matched only one product, shown below

DNF18-110FIB-E



- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
- Fully insulated design provides protection from electrical shorts
- Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection
- UL Flammability UL 94V -2/HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600 V per UL 310

Part Number	DNF18110FIB-E
RoHS Compliancy Status	Compliant
Part Description	Female disconnect, nylon fully insulated, funnel entry, 22– 18 AWG, .110 X .032 tab size.
Product Type	Disconnects
CSA Certified	Yes
UL Listed	Yes
Height (In.)	0.16
Height (mm)	4.1
Length (In.)	0.71
Length (mm)	18.0
Width (In.)	0.19
Width (mm)	4.8
CE Compliant	No
Insulation	Nylon
Max. Ins.	0.120
Max. Ins. (mm)	3.0
Panduit Color Code	Red
Plating Type	Tinned
Pricing Description	Terminal Convenience Package
Tab Size (In.)	0.110 x 0.032
Tab Size (mm)	2.8 x 0.8
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-100A, CT-600-A, CT-1525‡, CT-2500‡
Wire Range	22 – 18 AWG
Wire Range (mm ²)	0.38 – 1.0
Min. Order UOM	PC
Min. Order Qty.	20
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.