

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFDNG18187FB- ..
 - Part Drawings
 - PDFSUPRAGRIP F..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) | Search Tips

 Text Search: 'DNG18-250FB-L'


Your search criteria matched only one product, shown below

DNG18-250FB-L



Patented Panduit Supra-Grip™ fully pre-insulated disconnects offer a funnel entry metal insulation grip.

- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
- Flared barrel extension integrated into stamping to provide insulation grip for double crimp requirements
- Fully insulated design provides protection from electrical shorts
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection
- Mates with DNF-FIMB family
- UL Flammability UL 94V-2/HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600 V per UL 310, where applicable

Part Number	DNG18250FB-L
RoHS Compliancy Status	Compliant
Note	DNG18250FB-L replaces DNG18250FB-C
Part Description	Supra-Grip Female Disconnect, nylon fully insulated, 22- 18 AWG, .250 x .032 tab size.
Product Type	Female Disconnect
CSA Certified	Yes
UL Listed	Yes
Height (In.)	0.22
Height (mm)	5.6
Length (In.)	0.93
Length (mm)	23.6
Width (In.)	0.35
Width (mm)	8.9
CE Compliant	No
Insulation	Nylon
Max. Ins.	0.126
Max. Ins. (mm)	3.26
Panduit Color Code	Red
Plating Type	Tinned
Pricing Description	Female Disconnect, double crimp, nylon fully insulated, 22 18 AWG, .250 x .032 tab size
Tab Size (In.)	0.250 x 0.032
Tab Size (mm)	6.3 x 0.8
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-1015
Wire Range	22 – 18 AWG
Wire Range (mm ²)	0.5 – 1.0
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.