


Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'F5LE3-10EM3'

Your search criteria matched only one product, shown below

F5LE3-10EM3




- Colour-specific keys mechanically and visually distinguish connections to prevent positive and negative unintentional insertion into unlike keyed or non-keyed ports and allows design flexibility and versatility for a more discrete network
- Factory terminated and 100% tested for insertion loss (all) and return loss (10Gig™ and SM). Assures high performance for increased up-time and lower cost of ownership
- Low smoke zero halogen meets IEC -60332 (LSZH) flame rating for standard compliant safety
- Singlemode endfaces UPC polished (55dB min. return loss) ensures a high quality endface for higher return loss to meet application requirements
- Every singlemode endface is 100% factory inspected in compliance with Telcordia GR -326-CORE, Issue 3 requirements to assure high performance
- Keyed LC 10Gig™ Patch Cords and Pigtails are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10Gb/s for link lengths up to 300 meters for OM3 at 850nm to assure high performance and reliability
- Test data supplied with each patch cord and pigtail establishes a performance reference to streamline maintenance and troubleshooting

streamline maintenance and troubleshooting

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G- Violet, H- Aqua, J- Rose, K- Slate, L- Brown, P- White, Q- Charcoal, R- Lavender, S- Peach, T- Steel Blue, V- Maroon and W- Mint.

Part Number	F5LE3-10EM3
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS.
Part Description	SC to LC (keyed E- Orange) connector, LSZH, multimode duplex patch cord, 1.6mm jacketed cable (one duplex SC connector on one end and one duplex keyed LC connector on the other end) – 50/125?m.
Product Type	Keyed LSZH Patch Cords
Length (m)	3
Fiber Compatibility	50/125?m
Fiber Cable Size	1.6mm
Fiber Cable Type	Jacketed
Connector 1 Type	SC Connector
Connector 2 Type	LC Connector- Keyed E (Orange)
Fiber Count	2
Flammability Rating	LSZH (Low Smoke Zero Halogen)
Key Type and Color	Keyed E- Orange
Pricing Description	SC to Keyed LC (EOrange), 50?m, Duplex, LSZH,3M
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.