

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)  Within Results


 **Text Search: 'F9D3-4M2Y'**

Your search criteria matched only one product, shown below

## F9D3-4M2Y



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR -326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Part Number	F9D3-4M2Y
RoHS Compliancy Status	Intended for use in fixed installations which are outside the scope of RoHS
Note	F9D3-4M2Y replaces F9D3-4M2
Part Description	SC to FC singlemode duplex patch cord (two SC connectors on one end and two FC connectors on the other end) - 9/125µm.
Product Type	Hybrid Patch Cords
Length (m)	2
Fiber Compatibility	9/125µm
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Singlemode
Connector 1 Type	SC Connector
Connector 2 Type	FC Connector
End Configurations	SC to FC
Fiber Count	2
Flammability Rating	Riser (OFNR)
Pricing Description	PC SC To FC 9µm Dupl 2m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.