



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'F9D6J-6JM2Y'

Your search criteria matched only one product, shown below

F9D6J-6JM2Y



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR -326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Part Number	F9D6J-6JM2Y
RoHS Compliancy Status	Compliant
Note	F9D6J-6JM2Y replaces F9D6J-6JM2
Part Description	FJ [®] Jack Module to F [®] Jack Module singlemode duplex patch cord (one F [®] Jack Module on each end) - 9/125 ^µ m.
Product Type	FJ [®] Patch Cords
Length (m)	2
Fiber Compatibility	9/125 ^µ m
Fiber Cable Size	3mm
Fiber Cable Type	Jacketed
Fiber Type	Singlemode
Connector 1 Type	FJ [®] Jack Module
Connector 2 Type	FJ [®] Jack Module
End Configurations	FJ [®] Jack to FJ [®] Jack
Fiber Count	2
Flammability Rating	Riser (OFNR)
Pricing Description	PC FJ Jack To FJ Jack 9 m Dupl 2m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.