

Search Results

Evaluate

- FAQ's
- Press Releases
- PANDUIT Fibe ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Mini-Com FJ ..

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips Within Results

 Text Search: 'FJJGM2.0CEI'

Your search criteria matched only one product, shown below

FJJGM2.0CEI



- TIA/EIA-604 FOCIS-6 compliant connectors
- Exceed TIA/EIA-568-B.3 requirements
- Insertion loss: 0.1dB average (multimode), 0.2dB average (singlemode)
- Return loss: >20dB (multimode), >40dB (singlemode)
- RJ45 small form factor duplex jack module -- double the port density in one module space
- Non-optical disconnect maintains data transmission under tensile loads for jacketed cable
- *Mini-Com*® Jack Modules snap in and out of all *Mini-Com*® telecommunications room products and work area outlets
- Each duplex jack module includes housing, cover, two ferrule assemblies, two crimp sleeves, one boot for 900µm buffered fiber, one boot for 3mm jacketed cable and one dust cap
- Can be clearly identified with labels and icons
- Fiber cable type: tight-buffered recommended
- Fiber cable size: 900µm buffered fiber, 3.0mm jacketed cable or 1.6mm – 2.0mm jacketed cable (noted in part description)

- For 250µm coated fiber termination, use 250 micron fiber build-up tube kit or fan-out kits
- Ferrule type: 2.5mm zirconia ceramic (highest durability for repeated matings)
- Field polish termination -- *PANDUIT*® recommends anaerobic adhesive
- Use field polish termination kit (FJKITG)

Part Number	FJJGM2.0CEI
RoHS Compliancy Status	Compliant
Part Description	FJ® Multimode Duplex Fiber Optic Jack Module with phosphor bronze split sleeves for 1.6mm – 2.0mm jacketed cable or 900µm buffered fiber installation.
Product Type	FJ® Jack Modules
Color	Electric Ivory
Fiber Compatibility	62.5/125µm / 50/125µm
Fiber Cable Size	1.6mm - 2.0mm or 900µm
Fiber Cable Type	Tight-buffered recommended
Fiber Type	Multimode
Termination Style	Field Polish
Ferrule Type	Zirconia Ceramic
No. of Module Spaces	1
Pricing Description	FJ Jack Module Multimode for 2.0mm Jacketed Cable EI
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.