

Search Results

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF FQZO-12-10 P
- Part Drawings
- PDF QuickNet SFQ..
- PDF Fiber Optic..
- Specification Sheets
- PDF QuickNet SFQ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'FQXO-6-3'

Your search criteria matched only one product, shown below


FQXO-6-3



- QuickNet™ SFQ Series MTP* Fiber Optic Cassettes are compatible with QuickNet™ Patch Panels for up to 96 fiber connections in 1RU with QAPP48HDBL QuickNet™ 48 -port Angled Patch Panel
- Low insertion loss of 0.5dB max. per cassette and .75dB max. per standard cassette; ensures system meets IEEE 802.3ae max. channel loss specification of <2.6dB
- Return loss: ?26dB (10Gig™ multimode), ?20dB (multimode), ?55dB (singlemode)
- Connect together with high -density female MTP* cable assemblies as interconnecting network segments for deploying a remote or data center location in minutes
- Significantly reduce installation time and labor by eliminating field connector terminations
- Factory terminated, assembled and 100% tested
- Insertion loss data provided on every fiber cassette
- Return loss data provided on all singlemode fiber cassettes
- Lifetime traceability of test data to a Q.C. number on each fiber cassette
- 10Gig™ OM3 50/125 ?m Fiber Cassettes are tested per IEEE 802.3ae 10 GbE to support

network transmission speeds up to 10 Gb/s for link lengths up to 300 meters at 850nm; backward compatible with all 50/125 ?m (OM2) MPO or MTP* system requirements

*MTP is a registered trademark of US Conec Ltd.

Part Number	FQXO-6-3
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS.
Part Description	Optimized 10Gig™ 50/125 ?m OM3 Three SC duplex adapters to one male MTP*; fiber optimized pre-terminated MTP* rear mount cassette provides low insertion loss of 0.5dB max. per fiber.
CE Compliant	No
Pricing Description	Optimized SFQ Fiber Cassette 10 GbE 50m OM3 6Fiber 3 Dupl SC to (1) MTP
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.