

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFInsulated Fe..
 - Specification Sheets
 - PDFFerrules wit ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'FSDXL84-12-C'

Your search criteria matched only one product, shown below

FSDXL84-12-C



- Wide sleeve provides a barrier against electrical shorts
- Inside diameter of sleeve suitable for wire with very thick insulation
- Meets DIN dimensional and color standards for single wire containment
- Funnel entry for faster insertion and lower installed cost
- Designed with a seamless barrel to contain loose wire strands for superior terminations
- Eases insertion of stranded wire into terminal blocks
- Multiple pin lengths available

Part Number	FSDXL84-12-C
RoHS Compliancy Status	Compliant
Part Description	Polypropylene insulated ferrules – single wire DIN expanded short circuit protection end sleeve.
Color	Blue
Length (In.)	1.00
Length (mm)	25.5
CE Compliant	No
Inside Diameter (In.)	0.24
Inside Diameter (mm)	6.0
Insulation	Polypropylene
Max. Wire Insul. Dia. (In.)	0.47
Pin Length (In.)	0.47
Pin Length (mm)	12.0
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-1004, CT-1104
Wire Range	6 AWG
Wire Range (mm ²)	16.0
Wire Strip Length (In.)	5/8
Wire Strip Length (mm)	15.9
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.