



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'FSP91255F150A'

Your search criteria matched only one product, shown below

FSP91255F150A



- Connectivity meets or exceeds TIA/EIA-568-B.3 and ISO/IEC 11801 performance requirements
- Jacketed cable is compliant with NFPA 262 (OFNP) flame rating
- MTP* (12-fiber) connectors are FOCIS -5 compliant
- Insertion loss per mated pair: 0.50dB typical, 0.75dB max.
- *PANDUIT* proprietary MTP* polishing provides low insertion loss and high return loss, minimizing variability for improved channel link loss performance
- Factory terminated and 100% tested for insertion loss (test data supplied with each assembly); singlemode and *10Gig*[™] Multimode Trunk Cable Assemblies are also tested for return loss
- TIA/EIA568-B.1-7 (Method A) standards based polarity supports 10 Gb/s, multimode, and singlemode fiber types, and allows infrastructure backwards compatibility for component interchangeability and a lower cost of ownership
- *10Gig*[™] laser optimized fiber is tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters at 850nm

- Application specific designs available to tailor configuration, reach, and breakout construction to application requirements; for more information contact *PANDUIT* or visit [www.panduit.com](#)

*MTP is a registered trademark of US Conec Ltd.

Part Number	FSP91255F150A
RoHS Compliance Status	Compliant
Part Description	Female MTP* to female MTP* 12 fiber 9/125µm OS1 singlemode plenum rated trunk cable assembly with pulling eye on one end.
Product Type	MTP* Trunk Cable Assemblies
Length (ft.)	150
Fiber Compatibility	9/125µm
Fiber Type	Singlemode
Connector 1 Type	Female MTP* Connector
Connector 2 Type	Female MTP* Connector
End Configurations	Female MTP* to Female MTP*
Fiber Count	12
Flammability Rating	Plenum (OFNP)
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.