

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFMTP Fiber Op ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'FX12D5-5M90Y'

Your search criteria matched only one product, shown below

FX12D5-5M90Y



- Pass all TIA/EIA-568-B.3 performance requirements
 - FOCIS-5 compliant
 - Insertion loss per mated pair: 0.50dB typical; 0.75dB max.
 - Tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters at 850nm with 50/125 μ m (OM3) laser optimized fiber
 - Backward compatible with all 50/125 μ m (OM2) MPO or MTP* system requirements
 - Factory terminated and 100% tested for insertion loss
 - Insertion loss and return loss data recorded for every 10Gig™ Multimode Interconnect Cable Assembly
 - Lifetime traceability of test data to a Q.C. number on each cable assembly
- * MTP is a registered trademark of US Conec Ltd.

Part Number	FX12D5-5M90Y
RoHS Compliancy Status	Compliant
Part Description	Female MTP* to female MTP* 12 fiber interconnect cable assembly (one female MTP* connector on each end on ribbon interconnect cable) – 10 GbE 50/125 μ m.
Product Type	MTP* 12 Fiber Interconnect Cable Assemblies
Length (m)	90
Fiber Compatibility	10 GbE 50/125 μ m
Fiber Type	Multimode
Connector 1 Type	MTP* Connector
Connector 2 Type	MTP* Connector
End Configurations	MTP* to MTP*
Fiber Count	12
Flammability Rating	Plenum (OFNP)
Pricing Description	MTP* MTP* Interconnect Cable Assembly 90m 10 GbE 50m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.