

Search Results

- Evaluate
  - FAQ's
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'FXOLE10-10M3'

Your search criteria matched only one product, shown below


### FXOLE10-10M3



- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Backward compatible for use with all 50/125 μm system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FXE10-10M1Y) with the desired length (FXE10-10M2Y for 2 meter length). The above lengths are stock items. For

other lengths, contact Customer Service for actual lead times.

Part Number	FXOLE1010M3
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS.
Part Description	LC to LC optimized multimode duplex patch cord, 1.6mm jacketed cable (one duplex LC connector on each end) – 10Gig™ 50/125 μm.
Product Type	LC Patch Cords
Length (m)	3
Fiber Compatibility	10 GbE 50/125μm
Fiber Cable Size	1.6mm
Fiber Cable Type	Jacketed
Fiber Type	Multimode
Cable Color	Aqua
Cable Type	Duplex
CE Compliant	No
Connector 1 Type	LC Connector
Connector 2 Type	LC Connector
End Configurations	LC to LC
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Pricing Description	LC to LC, Optimized OM3, Duplex, LSZH, 1.6mm jacketed cable, 3m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.