


Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'FZOLE310M1'

Your search criteria matched only one product, shown below


FZOLE3-10M1



- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 550 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Backward compatible for use with all 50/125 μm system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
- Highest quality flame retardant fiber optic cable with tight -buffered coating on each optical fiber

Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtaills are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FZPE10 -10M1) with the desired length (FZPE10 -10M2 for 2 meter length). The above lengths are stock items. For

other lengths, contact Customer Service for actual lead times.

Part Number	FZOLE3-10M1
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	SC to LC Patch Cord, Optimized OM4, 0.15 dB IL Loss, Duplex, LSZH, 1.6mm jacketed cab – 1m.
Product Type	Hybrid Patch Cords
Length (m)	1
Fiber Compatibility	10 GbE 50/125μ
Fiber Cable Size	1.6mm
Fiber Cable Type	Jacketed Cable
Fiber Type	Multimode
Connector 1 Type	SC Connector
Connector 2 Type	LC Connector
End Configurations	SC to LC
Fiber Count	2
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Pricing Description	SC to LC, Optimized OM4, Duplex, LSZH, 1.6mm jacketed cable, 1m
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.