



GP6™ PLUS Category 6 Standard Density Bases

- Exceed ANSI/TIA-568-C.2 Category 6 standard
- Ideal for use in cross-connects and consolidation point applications
- Highly visible color-coded wiring slots ease wiring
- Sturdy one-piece design
- Available with or without mounting legs for a variety of mounting options
- Multiple mounting holes available



GPB24-X



GPBW24-X



GPB72-X



GPBW72-X

Part Number	Part Description	Std. Pkg. Qty.
96-Pair (24-Port) Category 6 Punchdown Base		
GPB24-X	Positions and holds UTP wire for termination with Category 6 connecting blocks.	10
96-Pair (24-Port) Category 6 Punchdown Base – with Legs		
GPBW24-X	Positions and holds UTP wire for termination with Category 6 connecting blocks, includes mounting legs.	10
288-Pair (72-Port) Category 6 Punchdown Base		
GPB72-X	Positions and holds UTP wire for termination with Category 6 connecting blocks.	10
288-Pair (72-Port) Category 6 Punchdown Base – with Legs		
GPBW72-X	Positions and holds UTP wire for termination with Category 6 connecting blocks, includes mounting legs.	10

Termination tool available on page B.79 of SA-NCCB51.

For rack mount applications see page B.81 of SA-NCCB51.

Cable requirement: terminates most 22 – 26 AWL solid or stranded IWO wire with a 0.050" (1.27mm) max o.d., either PVC or plenum rated.

To ensure optimal performance, Panduit recommends use with other Panduit Category 6 components.

Can be clearly identified with label holders and recommended labels shown below.

GP6™ PLUS Standard Density Tower Kit

- Ideal for use in cross-connects, consolidation point, and wall mount applications
- Tower provides vertical feeder cable management
- Supplied with tower, bases, 4-pair connecting blocks, label and label holders



Part Number	Part Description	Std. Pkg. Qty.
GPKT724Y	288-pair (72-port) Category 6 punchdown standard density GP6™ PLUS Tower Kit.	1

Termination tool available on page B.79 of SA-NCCB51.

Cable requirement: terminates most 22 – 26 AWL solid or stranded IWO wire with a 0.050" (1.27mm) max o.d., either PVC or plenum rated.

To ensure optimal performance, Panduit recommends use with other Panduit Category 6 components.