


Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFH___X044H*T
 - Specification Sheets
 - PDFMilitary Gra..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'H075X044H2T'

Your search criteria matched only one product, shown below

H075X044H2T



- Labels offer crisp, clear legends with superior legibility
- Meets UL Standard 224 for flammability and AMS -DTL-23053/5C (Class 1 and Class 3)
- Will meet MIL-M-81531, MIL-STD202F, and MIL-STD-883E when printed with RMH4BL or RHH4BL -S ribbons
- Shrink ratio 3:1
- Pre-cut flattened polyolefin is both thermal transfer and dot matrix printable and supplied roll mounted on plastic carrier
- Panduit labeling software packages include all label formats for quick and easy label production

Part Number	H075X044H2T
RoHS Compliancy Status	Compliant
Part Description	Yellow, 1/4" diameter polyolefin, 1000/roll.
Material	3:1 Flattened Polyolefin
Color	Yellow
Length (In.)	0.44
Length (mm)	11.2
Width (In.)	0.75
Width (mm)	19.1
Max. Wire O.D. (In.)	0.25
Max. Wire O.D. (mm)	6.4
Min. Cable O.D. (In.)	0.08
Min. Cable O.D. (mm)	2.0
Nominal Cable O.D. (In.)	0.08 - 0.25
Nominal Cable O.D. (mm)	2.0 - 6.4
Pricing Description	Heat Shrink Label, 0.25" (6.35mm) Dia., Yellow
Wire Range	16 – 10 AWG
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.