

Search Results

Evaluate

- FAQ's
- Product Bulletins
- PDFHook and Loo..

Design a Solution

- Catalog Cut Sheet
- PDFUCT3SX0 Pro
- Part Drawings
- PDFTape-Ty Cabl

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'HLTT1.5S-Q20'

Your search criteria matched only one product, shown below

HLTT1.5S-Q20



- Ultra-thin materials provide a low -profile, flexible construction
- Non-slip applicator prevents lateral movement of tie and allows tighter fastening of cable bundle
- Leaves no residue and is safe to use on high -performance cabling
- Pre-cut ties eliminate cutting ties to length and staging them for each job
- Adjustable, releasable, and reusable
- Available in black

Part Number	HLTT1.5SQ20
Part Description	Low profile Hook & Loop Tape-Ty Cable Tie w/non-slip leader, 7"L x 0.75"W. 25 ties on core-less reel.
Length (In.)	7.00
Length (mm)	177.8
Width (In.)	0.75
Width (mm)	19.1
CE Compliant	No
Max. Bundle Diameter (In.)	1.50
Max. Bundle Diameter (mm)	38.1
Min. Loop Tensile Strength (Lbs.)	30
Min. Loop Tensile Strength (N)	133.4
Packaging Method	25 ties on core-less reel
Pricing Description	Low profile Hook & Loop Tape-Ty Cable Tie w/non-slip leader, 7"L x 0.75"W
Min. Order UOM	PK
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.