

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIE

WITH PLUG CAPS

PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
IUTPCH3BLY	3 FT.	1.97 lbs/10 PCS (735.3 g/10 PCS)
IUTPCH5BLY	5 FT.	2.53 lbs/10 PCS (944.3 g/10 PCS)
IUTPCH7BLY	7 FT.	3.09 lbs/10 PCS (1153.3 g/10 PCS)
IUTPCH10BLY	10 FT.	3.93 lbs/10 PCS (1784.2 g/10 PCS)
IUTPCH15BLY	15 FT.	5.31 lbs/10 PCS (1981.9 g/10 PCS)
IUTPCH20BLY	20 FT.	6.70 lbs/10 PCS (2500.7 g/10 PCS)

NOTES:

- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [] ARE IN METRIC.
4. NUT ON STRAIN RELIEF TAIL MUST BE TORQUED TO 20 IN-LBS TO MAINTAIN IP67 RATING
5. CABLE MEETS CATEGORY 5E REQUIREMENTS AND CURRENT ODVA REQUIREMENTS FOR INDUSTRIAL CABLE.

WITHOUT PLUG CAPS

PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
IUTPCHNC3BLY	3 FT.	1.53 lbs/10 PCS (692.84 g/10 PCS)
IUTPCHNC5BLY	5 FT.	1.99 lbs/10 PCS (901.84 g/10 PCS)
IUTPCHNC7BLY	7 FT.	2.45 lbs/10 PCS (1110.84 g/10 PCS)
IUTPCHNC10BLY	10 FT.	3.84 lbs/10 PCS (1741.74 g/10 PCS)
IUTPCHNC15BLY	15 FT.	4.28 lbs/10 PCS (1939.41 g/10 PCS)
IUTPCHNC20BLY	20 FT.	5.42 lbs/10 PCS (2458.24 g/10 PCS)

T568A WIRING

PLUG POSITION

1
2
3
4
5
6
7
8

CABLE WIRE
WHITE GREEN
GREEN
WHITE ORANGE
BLUE
WHITE BLUE
ORANGE
WHITE BROWN
BROWN

PLUG CAPS - ON IUTPCH*BLY PARTS ONLY

PART NUMBER

IUTPCH*BLY, IUTPCHNC*BLY

TITLE

CATEGORY 5E INDUSTRIALNET, UTP,
SOLID, PATCH CORD WITH PANDUIT PLUGS

CUSTOMER DRAWING

ITEM REVISION NAME

M02479LX/00

DATASET FILE NAME

M02479LX_DC311/00B


UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.x ±

.xx ± .03 [.8]

.xxx ± .010 [.3]

ANGLES ±



THIRD ANGLE
PROJECTION

MATERIAL:

DRAWING NUMBER:

02479-311

DRAWN BY

LZ

DATE

3-18-06

CHK

WJC

SCALE

NONE

SHT 1 OF 1

SIZE

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	6/13/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-311
R	3-18-06	LZ	WJC	RMD	RELEASED TO PRODUCTION	02479-311