

Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDFJ-Pro Cable..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'JP131W-L3'

Your search criteria matched only one product, shown below

**JP131W-L3**



- Complete horizontal and vertical 1" bend radius control helps prevent degradation of cable performance
- UL 2043 and CAN/ULC S102.2 listed and are suitable for use in air handling spaces
- Durable non-metallic J Hook materials provide the ability to manage and support a large number of cables
- Pre-riveted assemblies allow for attachment to ceilings, beams, threaded rods, drop wires and under floor supports to meet requirements of a variety of applications
- Wide cable support base prevents pinch points that could cause damage to cables
- Cable tie channel allows user to easily install 3/4" Tak -Ty® Cable Ties to retain cable bundle

Part Number	JP131W-L3
RoHS Compliancy Status	RoHS directive is not applicable
Part Description	J Hook for wall mount applications. One 1/4" (M6) mounting hole for user supplied screw.
Material	Nylon 6.6
Color	Orange
10Gig (.33")	18
CAT 5E (.193")	29
CAT 6 (.248")	25
CAT 6Plus (.26")	15
CE Compliant	No
Max. Bundle Capacity (In.)	1.31
Max. Bundle Capacity (mm)	33.3
Max. Static Load (Kg)	11.30
Max. Static Load (Lbs.)	25
Pricing Description	J-Pro 1.31" Cable Support System Wall Mount, Orange
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.