

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFJP75WL20 Pr
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'JP75WP2-L20'

Your search criteria matched only one product, shown below

JP75WP2-L20



- Complete horizontal and vertical 1" bend radius control helps prevent degradation of cable performance
- UL 2043 and CAN/ULC S102.2 listed and are suitable for use in air handling spaces
- Durable non-metallic J Hook materials provide the ability to manage and support a large number of cables
- Pre-riveted assemblies allow for attachment to ceilings, beams, threaded rods, drop wires and under floor supports to meet requirements of a variety of applications
- Wide cable support base prevents pinch points that could cause damage to cables
- Cable tie channel allows user to easily install 3/4" Tak -Ty® Cable Ties to retain cable bundle

Part Number	JP75WP2L20
Part Description	J Hook for powder actuated installation on walls. One 5/32" (M4) mounting hole and one 1/4" (M6) mounting hole for user supplied fasteners.
Material	Nylon 6.6 with metal attachments
Color	Black
CAT 5E (.193")	10
CAT 6 (.248")	8
CAT 6Plus (.26")	5
CE Compliant	No
Max. Bundle Capacity (In.)	0.75
Max. Bundle Capacity (mm)	19.0
Max. Static Load (Kg)	6.8
Max. Static Load (Lbs.)	15
Pricing Description	J-Pro Cable Support System Wall Mount With Bracket
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.