

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'LCCX2/0-14BF-X'

Your search criteria matched only one product, shown below

**LCCX2/0-14BF-X**



For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Long barrel maximizes number of crimps and provides premium wire pull -out strength and electrical performance
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV\*\* and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- Meets J-STD-607-A and TIA-942 requirements for network systems grounding applications
- Available with NEMA hole sizes and spacing

Note: These flex conductor lugs are manufactured for use with AWG wire only.

Part Number	LCCX2/0-14BF-X
RoHS Compliancy Status	Compliant
Part Description	Flex lug, long barrel, 2/0 AWG, 2hole, 1/4" stud holes, .75 hole spacing, 90° angle tongue.
Length (In.)	2.42
Length (mm)	61.5
Class G,H, I, K, M	2/0 AWG
Diesel Locomotive	2/0 AWG
Stud Hole Size (In.)	1/4
Stud Hole Spacing (In.)	.75
Tongue Width (In.)	.96
Barrel Length (In.)	1.50
Angle	90°
Barrel Length (mm)	38.1
CE Compliant	No
CE Marking	No
Panduit Color Code	Black
Panduit Die Index No.	P45
Pricing Description	Copper Compression Lug, 2 Hole, 2/0 AWG Flex, 1/4" (6.4mm) Stud, 90° Bent
Stud Hole Size (mm)	M6
Tongue Thickness	.13
Tongue Type	Standard
Tongue Width (mm)	24.4
Wire Range (mm <sup>2</sup> )	70
Wire Strip Length (In.)	1 9/16
Wire Strip Length (mm)	40.0
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	13
T&B Die Index No.	45
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.