



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'LDPH5WH6-A'

Your search criteria matched only one product, shown below

LDPH5WH6-A



Pan-Way® Type LDPH Surface Raceway is a single channel raceway designed to route, protect and conceal data, voice, video, fiber-optic and/or power cabling.

- UL and CSA rated 600 V; meets UL 5A and CSA C22.2 No. 62.1 -03 standards; FT4 rated
- Two-piece hinged design allows cables to be laid in
- Tamper resistant
- Factory applied adhesive backing speeds installation
- Terminates using surface mount outlet box solutions or *PANDUIT*® *Mini-Com*® Surface Mount Boxes

All AW (Arctic White) and two and three meter products are only available outside of North America as a standard item. Contact customer service for minimum order quantities, stock and other color availability.

Part Number	LDPH5WH6A
RoHS Compliancy Status	Compliant
Part Description	Tamper resistant two-piece latching surface raceway. Supplied with pre -punched mounting holes and factory applied adhesive tape. Available in 6', 8', and 10' lengths.
Product Type	Power Rated Raceway
Color	White
CSA 22.2 No.6293	Yes
UL5A Listed	Yes
Length (ft.)	6
CE Compliant	Yes
CE Marking	Yes
Pricing Description	LDPH5 Hinged, 2piece Power Rated Raceway with Adh. 6ft.
Product Length	6'
Product Size	5
Raceway Size	1.02" x .55" (26.0mm x 14.0mm)
Min. Order UOM	FT
Min. Order Qty.	6
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.