

Search Results

Evaluate

- FAQ's
- Press Releases
- PANDUIT Intr.
- Product Bulletins
- PDFPanduit Perm.

Design a Solution

- Catalog Cut Sheet
- PDFMIM094 Produ
- Part Drawings
- PDFMetal Marker..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'MMP350H-M'

Your search criteria matched only one product, shown below

MMP350HM



- Provides permanent identification of pipes, conduit, valves, cables and equipment in harsh environments
- Designed for use with PANDUIT ® Pan-Steel® Stainless Steel Cable Ties for fast installation at lowest installed cost
- All marker plates/tags can be embossed or laser etched with PANDUIT Factory Custom Marking Service
- For on-site custom marking use the metal indenting machine

Part Number	MMP350HM
RoHS Compliancy Status	Compliant
Part Description	Marker plate, four holes, 304 Stainless Steel, heavy cross section, 3.50" x .75".
Product Type	Marker Plate
Material	304 Stainless Steel
Color	Natural
Length (In.)	3.50
Length (mm)	89.0
Width (In.)	0.75
Width (mm)	19.0
Max. Lines	3
Mounting Method	Heavy Cross Section MLT Cable Ties
Pricing Description	Marker Plate, 304 SS, 4 Hole, 3.5" x75" x .010" (89mm x 19mm x .25mm) thk
Thickness (In.)	0.010
Thickness (mm)	0.25
Used with Pan-Steel Ties	MLT-H
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.