

**Search Results**

- Evaluate
  - FAQ's
- Design a Solution
  - Specification Sheets
  - PDFPanPlug 30 A..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

Text Search: 'MP530-M'

Your search criteria matched only one product, shown below

**MP530-M**



- Meets all applicable ANSI/TIA-968-A and IEC 60603-7 requirements
- Patented tangle-free plug latch prevents snags and provides easy release saving time on frequent moves, adds, and changes
- Simplified termination method with cable manager insert provides excellent performance and additional strain relief
- Contacts plated with 50 microinches of gold for superior performance
- Terminates 30 AWG, 100 ohm, stranded or solid conductor; conductor insulation diameters between 0.021 in. - 0.024 in. (0.533mm - 0.610mm); cable jacket diameters between 0.140 in. - 0.160 in. (3.55mm - 4.06mm)

|                              |   |
|------------------------------|---|
| Part Number                  | MP530M  |
| Part Description             | 8-position, 8-wire modular plug, for use with 30 AWG Category 5e, UTP Copper Cable. |
| Product Type                 | Modular Plug  |
| Color                        | Clear   |
| Performance Level            | Category 5e/Class D   |
| Pricing Description          | 30 AWG, Category 5e, UTP, Modular Plug, 1000 Pack                                   |
| Min. Order UOM               | PC  |
| Min. Order Qty.              | 1   |
| BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>  |
| Add to Favorite Product List | <input type="button" value="e"/>  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.