

Products

- Products Overview
- Product Search**
- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFLCCX8-10A-L
 - Part Drawings
 - PDFCopper, Long..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Product Search >

Current refinements (click to remove) Search Tips

Part Number > LCCX8-10AB-L

Your search criteria matched only one product, shown below

LCCX8-10AB-L



For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Long barrel maximizes number of crimps and provides premium wire pull -out strength and electrical performance
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with Panduit and specified competitor crimping tools and dies
- Meets J-STD-607-A and TIA-942 requirements for network systems grounding applications
- Available with NEMA hole sizes and spacing

Note: These flex conductor lugs are manufactured for use with AWG wire only.

Part Number	LCCX8-10AB-L
RoHS Compliancy Status	Compliant
Part Description	Flex lug, long barrel, #8 AWG, slotted 2hole, #10 stud holes, .63– .75 hole spacing.
Material	Tin-Plated Copper
CSA Certified	Yes
UL Listed	Yes
Length (In.)	2.14
Length (mm)	54.4
Class G,H, I, K, M	#8 AWG
Diesel Locomotive	#8 AWG
Stud Hole Size (In.)	#10
Stud Hole Spacing (In.)	0.63 – 0.75
Tongue Width (In.)	0.41
Barrel Length (In.)	0.70
Angle	Straight
Barrel Length (mm)	17.8
CE Compliant	No
Figure No.	2
Panduit Color Code	Red
PANDUIT Die Color & Die No.	Red P21
Panduit Die Index No.	P21
Pricing Description	Copper Comp. Lug, 2 Hole, #8 AWG Flex, #10 (4.8mm) Stud, Slotted Tongue
Stud Hole Size (mm)	4.8
Tongue Thickness	0.08
Tongue Type	Standard
Tongue Width (mm)	10.4
Tool	CT-1700, CT-930, CT-2931, CT-2931/E
Wire Strip Length (In.)	3/4
Wire Strip Length (mm)	19.0
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	49
T&B Die Index No.	21
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.