

Products

- Products Overview
- Product Search**
- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFLCD10-10AH-L
 - Part Drawings
 - PDFCopper, Stan..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips

Part Description > Two-hole, standard barrel with window, 45° angle tongue, #2 AWG wire, 5/16" stud hole, .75" hole spacing.

Your search criteria matched only one product, shown below

LCD2-56BH-Q



For Use with Stranded Copper Conductors

- Color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with Panduit and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range -taking capability when crimped with Panduit ® Uni-Die™ Dieless Crimping Tools‡
- **Tested by Telcordia– meets NEBS Level 3**
- American Bureau of Shipping Approved
- Available with NEMA hole sizes and spacing

#10 lugs are not tested to NEBS Level 3 requirements.

Note: These code conductor lugs are manufactured for use with AWG wire only.

Part Number	LCD2-56BH-Q
RoHS Compliancy Status	Compliant
Part Description	Two-hole, standard barrel with window, 45° angle tongue, #2 AWG wire, 5/16" stud hole, .75" hole spacing.
Product Type	Compression Connectors- Lugs
Material	Tin-Plated Copper
CSA Certified	Yes
UL Listed	Yes
Length (In.)	2.36
Length (mm)	59.9
Copper Conductor Size	#2 AWG
Stud Hole Size (In.)	5/16
Stud Hole Spacing (In.)	0.75
Tongue Width (In.)	0.66
Barrel Length (In.)	0.88
Angle	45°
Barrel Length (mm)	22.4
Bolt Dia.	0.32
CE Compliant	No
Clearance	0.44
Panduit Color Code	Brown
Panduit Die Index No.	P33
Pricing Description	Copper Compression Lug, 2 Hole, #2 AWG, 5/16" (7.9mm) Stud, 45° Bent
Stud Hole Size (mm)	7.9
Tongue Thickness	0.10
Tongue Type	Standard
Tongue Width (mm)	16.8
Wire Strip Length (In.)	15/16
Wire Strip Length (mm)	23.8
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	10
T&B Die Index No.	33
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.