

Search Results

Evaluate

- FAQ's
- Product Bulletins
- PDFPan-Steel MS..

Design a Solution

- Catalog Cut Sheet
- PDFMS4W75T30Q2
- PDFMS4W75T30Q2
- Part Drawings
- PDFStainless St..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'MS6W75T30-Q2'

Your search criteria matched only one product, shown below

MS6W75T30-Q2



- Fold over design provides high -retained tension in mechanical fastening and cable bundling applications
- After tensioning, cut end is locked inside low profile buckle – no sharp edges
- Can be used in a wide range of indoor, outdoor, and underground (including direct burial) applications
- Smooth surfaces and rounded edges assures cable protection and worker safety
- Available in AISI 201 (3/4 width only) and 304 stainless steel for general -purpose applications
- Available in AISI 316 stainless steel for the most corrosive environments

Part Number	MS6W75T30Q2
RoHS Compliancy Status	Compliant
Part Description	Stainless steel strap, 201 AISI stainless steel.
Color	Natural
Length (In.)	26.5
Length (mm)	673
Width (In.)	0.75
Width (mm)	19.1
Max. Bundle Diameter (In.)	6.0
Max. Bundle Diameter (mm)	152
Max. Combined Bundle Dia. (In.)	3.0
Max. Combined Bundle Dia. (mm)	76
Min. Bundle Diameter (In.)	1.00
Min. Bundle Diameter (mm)	25.4
Min. Loop Tensile Strength (Lbs.)	1200
Min. Loop Tensile Strength (N)	5340
Pricing Description	MS Strapping, 201 SS, 0.75" (19.0mm) Wd, 26.5" (673mm), 0.030" (0.76mm) thk
Strap Breaking Strength (Lbs.)	2400
Strap Breaking Strength (N)	10656
Temperature Range	-80°C– 538°C
Thickness (In.)	0.030
Thickness (mm)	0.76
Tool	BT75SDT
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.