



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'NK5E88MWH-Q'

Your search criteria matched only one product, shown below

NK5E88MWH-Q



- Category 6 and 5e jack modules meet or exceed all performance requirements including ACR, ELFEXT and Return Loss
- Bulk packaged for high volume installations to further speed installation and reduce on-site waste
- No punchdown tool required for Category 5e, optional termination tool ensures conductors are fully terminated
- 8 position, 8 wire Keystone modules coded for T568A or T568B
- Terminates 4 -pair 24 and 22 AWG 100 Ohm solid unshielded twisted pair cable
- Color coded sled indicates performance category
- Maintains twists of UTP cable ensuring optimal channel and link performance
- Compatible with *NetKey*[™] Keystone Faceplates, Surface Mount Boxes, Modular Patch Panels and Keystone Adapter Panel ‡

Part Number	NK5E88MWH-Q
RoHS Compliancy Status	Compliant
Part Description	Category 5e, 8-position, 8-wire Keystone jack module.
CE Compliant	No
CE Marking	No
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.