

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- DWG-NetKey Categ..

- PDFNetKey Categ..

- DXF-NetKey Categ..

- Specification Sheets

- PDFNetKey Categ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Install & Maintain

- Installation Instructions

- PDFNetKey Categ..

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'NK5EPP24P'

Your search criteria matched only one product, shown below

NK5EPP24P



- Meets Category 5e/Class D performance requirements
- Molded design made of polymer material for improved flexibility and durability
- Punchdown style termination on back of patch panel
- Universal T568A and T568B color -coded wiring schemes included
- Terminates 4 -pair 22 to 26 AWG 100 ohm unshielded twisted pair cable
- Accepts icons for port identification
- Includes pre -numbered labels with writable surface on back of label and molded in numbering on front and back of panel to manage and organize installation

Part Number	NK5EPP24P
RoHS Compliancy Status	Compliant
Part Description	Category 5e, 24-port molded punchdown patch panel, 1 RU. Mounts to standard 19" racks or cabinets with enclosed mounting hardware.
Product Type	Punchdown Patch Panel
CE Compliant	Yes
No. of Module Spaces	24
No. of Rack Spaces	1
Patch Panel Style	Flat
Performance Level	Category 5e/ClassD
Pricing Description	NK All Molded Punchdown Patch Panel, Cat 5e, Flat, 24 Port, 1 RU
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.