

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings
- PDF-Next Generat ...
- Specification Sheets
- PDF-TX6A 10Gig K ...

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'UTPK6A14OR'

Your search criteria matched only one product, shown below

UTPK6A14OR



- Include all of the same features as the TX6A™ 10Gig™ UTP Patch Cords with the added benefit of visual and mechanical security
- Mechanical keyed configurations prevent unintentional insertion into adjacent ports (6 versions)
- Color-coded for easy identification
- Exceed ANSI/TIA-568-C.2, ISO 11801 Class E_A Edition 2.1 and IEEE 802.3an-2006 channel requirements for supporting 10GBASE-T
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired T568B
- Constructed of TX6A™ 10Gig™ 23 AWG stranded UTP copper cable (nominal cable diameter is .275 inches) and TX6™ PLUS Modular Plugs for superior performance
- Plug meets all applicable ANSI/TIA-968-A requirements and exceeds IEC 60603-7 specifications
- Slender strain relief boot provides easy access in high density applications
- Plug uses an integral pair manager to optimize performance and consistency by reducing untwisting of conductors within the plug
- Plug performance in center of TIA/EIA component range, ensuring interoperability and 10GBASE-T Ethernet channel performance
- Labels on patch cords provide identification of performance level, length, and quality control number
- Patented tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Optional Patch Cord Color Bands snap on and off individual patch cords offering endless color-coding options

• Part Number	UTPK6A14OR
• RoHS Compliancy Status	Compliant
• Part Description	Keyed, Category 6A, 10Gb/s UTP patch cord with TX6™ PLUS Keyed Modular Plug on one end and TX6™ PLUS Non-Keyed Modular Plug on the other end.
• Product Type	Keyed Copper Patch Cord
• Color	Orange
• Length (ft.)	14
• Length (m)	4.27
• Cable Color	Orange
• Cable Type	UTP
• CE Compliant	No
• Connector 1 Type	RJ45 8(8)
• Connector 2 Type	RJ45 8(8)
• Flammability Rating	CM
• Performance Level	Category 6A/Class EA
• Pricing Description	Keyed Copper Patch Cord, Cat 6A, Orange UTP Cable, 14 Feet
• Termination End 1	Keyed Modular Plug
• Termination End 2	Non-Keyed Modular Plug
• Wiring Scheme	T568B
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.