





CJH5E88TGIG

UTP Jack Module

Category 5e, RJ45, 8-position, 8-wire spring shuttered universal jack module. International Gray.



Specifications

Performance Level	Category 5e
Termination Style	Giga-TX (TG Style)
Module Type	Mini-Com
Wiring Scheme	T568A/T568B
Maximum Storage Temperature (°C)	70
Maximum Storage Temperature (°F)	158
Minimum Storage Temperature (°C)	-40
Minimum Storage	-40















Color	International Gray
Application	Unshielded
Material	ABS/Polycarbonate
Operating Temperature	14°F to 149°F (-10°C to 65°C)
Overall Depth (In.)	1.5
Overall Depth (mm)	38.1
Overall Height (In.)	0.71
RoHS Compliancy Status	Compliant
Min. Order Qty.	1

Temperature (°F)

Packaging Details

UPC	61305601485	Std. Ctn. Qty.	50
Std. Pkg. Qty.	1	Std. Ctn. Volume (cf)	0.1605
Std. Pkg. Volume (cf)	0.0032		

Resources

Selection Guides	Mini-Com Jack Module Selection Guide - "TG Style" Termination: COSG09	US English	PDF	473.91KB		
Part Drawings	Customer drawing for CJH5E88TG spring shuttered jack module	US English	PDF	220.92KB		
Specification Sheets	Mini-Com® TX5e™ UTP Jack Modules: COSP316	US English	PDF	196.88KB		
Part Drawings	Customer drawing for CJH5E88TG spring shuttered jack module DWG	US English	DWG	42.09KB		
Part Drawings	Customer drawing for CJH5E88TG spring shuttered jack module DXF	US English	DXF	3.85MB		
Specification Sheets	45° Angled Wire Caps for TX6A, TX6 PLUS TX5e Mini-Com® UTP Jack Modules: COSP406	US English	PDF	795.37KB		
Installation Documents	TX6 PLUS and TX5e UTP Jack Modules	US English	PDF	1.33MB		

Related Products



CJ688TGBU

The Category 6, RJ45, 8-position, 8-wire, UTP Mini-Com® universal jack module has TG-style termination and is blue.

CJ688TGBL

The Category 6, RJ45, 8-position, 8-wire, UTP Mini-Com® universal jack module has TG-style termination and is black.

CJS6X88TGY

Category 6A, RJ45, 10 Gb/s, 8-position, 8-wire universal shielded black module with integral shield.



Email Support

Email support available
24/7



800-777-3300

Monday through Thursday
7:00 am-6:30 pm CST
Friday 7:00 am-6:00 pm
CST



Where to Buy

Find a Panduit Distributor
or Partner

ABOUT US

Research and Development
Media Resources
World Headquarters
Awards
Partner Ecosystem

CAREERS AT PANDUIT

THE HUB – PARTNER PORTAL

PRODUCT REGISTRATION

PANDUIT CONNECTIONS BLOG



GET OUR CATALOG

Download the PDF or request a copy be
mailed to you.

Which catalog would you like? ▼

▶ DOWNLOAD ▶ REQUEST COPY

