



Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings
- PDF-NetKey Cat 6 ..
- Specification Sheets
- PDF-NetKey Categ ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'NK6PC20BUY'

Your search criteria matched only one product, shown below

NK6PC20BUY



- Meets Category 6 performance requirements
- Tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Constructed of enhanced performance 24 AWG stranded UTP cable
- 100% performance tested

• Part Number	NK6PC20BUY
• RoHS Compliancy Status	Compliant
• Part Description	Category 6, UTP patch cord with modular plugs on each end.
• Product Type	Copper Patch Cord
• Color	Blue
• Length (ft.)	20
• Length (m)	6.10
• BMEcat - Cable color	Blue
• Boot Color	Clear
• Cable Color	Blue
• Cable Type	U/UTP
• CE Compliant	No
• Connector 1 Type	RJ45 8(8)
• Connector 2 Type	RJ45 8(8)
• Flammability Rating	CM
• No. of Pairs	4
• Performance Level	Category 6/Class E
• Pricing Description	NK Copper Patch Cord, Category 6, Blue UTP Cable, 20 Feet
• Termination End 1	Modular Plug
• Termination End 2	Modular Plug
• Wiring Scheme	T568B
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.