

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'UTPSP14BUY-Q'

Your search criteria matched only one product, shown below

UTPSP14BUY-Q



- Exceed ANSI/TIA-568-C.2 Category 6 and ISO 11801 Class E standards
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired T568B
- Constructed of Category 6, 24 AWG UTP stranded cable and TX6™ PLUS Modular Plugs; plug contacts plated with 50 microinches of gold for superior performance
- Plug meets all applicable ANSI/TIA/EIA-968-A requirements and exceeds IEC 60603-7 specifications
- Slender strain relief boot provides easy access in high density applications
- Plug uses an integral pair manager to optimize performance and consistency by reducing untwisting of conductors within the plug
- Perform in center of TIA/EIA component range, ensuring interoperability and excellent performance
- Labels on patch cords provide identification of performance level, length, and quality control number
- Patented tangle-free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Optional patch cord color bands snap on and off individual patch cables offering endless color-coding options
- Optional RJ45 plug lock-in device blocks unauthorized removal of cable, IP phone, other networking equipment, or critical connection
- Third party tested for Category 6 component compliance

| | |
|--------------------------------|--|
| • Part Number | UTPSP14BUY-Q |
| • RoHS Compliancy Status | Compliant |
| • Part Description | Category 6, UTP patch cord with TX6™ PLUS Modular Plugs on each end. |
| • Product Type | UTP Patch Cord |
| • Color | Blue |
| • Length (ft.) | 14 |
| • Length (m) | 4.27 |
| • Boot Color | Clear |
| • Cable Type | UTP |
| • CE Compliant | No |
| • Connector 1 Type | RJ45 8(8) |
| • Connector 2 Type | RJ45 8(8) |
| • Flammability Rating | CM |
| • Performance Level | Category 6 |
| • Pricing Description | Copper Patch Cord, Cat 6, Blue UTP Cable, 14 Feet, Bulk Packaged |
| • Termination End 1 | Modular Plug |
| • Termination End 2 | Modular Plug |
| • Wiring Scheme | T568B |
| • Min. Order UOM | PC |
| • Min. Order Qty. | 25 |
| • BOM Qty. (# of Pkgs.) | <input type="text" value="0"/> |
| • Add to Favorite Product List | <input type="checkbox"/> |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.