



Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF-QuickNet HDQ ..
 - Specification Sheets
 - PDF-QuickNet Cas ..
 - PDF-QuickNet HDQ ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'F1RCXN-9612-10F'

Your search criteria matched only one product, shown below

F1RCXN-9612-10F



Quicknet™ HDQ Series High Density Fiber Optic Cassettes:

- Mounts to standard 19" rack rails
- Low insertion loss of 0.5dB max, per optimized cassette and 0.75dB max. per standard cassette; ensures system meets IEEE 802.3ae max. channel loss specification of < 2.6dB
- Return loss: ≥ 26dB
- Adapter housing colors follow TIA/EIA - 568-C.3 suggested color identification scheme
- Connect together with high-density female MTP* cable assemblies as interconnection network
- Significantly reduce installation time and labor by eliminating field connector termination
- Factory terminated, assembled, and 100% tested
- Insertion loss data provided on every fiber cassette
- Lifetime traceability of test data to a Q.C. number
- 10Gig OM3 50/125um fiber cassettes are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters and up to 550 meters for OM4 at 850 nm; backward compatible with all 50/125um (OM2) MPO or MTP system

requirements

Quicknet™ Cassette Rear Cable Manager:

- Mounts horizontally to standard 19" rack rails
- Fiber Management Slack Spools can be used to manage MTP Interconnect Cable

| | |
|--------------------------------|---|
| ▪ Part Number | F1RCXN-9612-10F |
| ▪ RoHS Compliancy Status | Compliant |
| ▪ Part Description | QuickNet™ HDQ Series High Density Fiber Optic Cassette; 1RU 96-fiber C-type labeling; 10Gb OM3 12-fiber MTP to LC Pre-terminated– flipped polarity. |
| ▪ Pricing Description | 12 Fiber High Density OM3 10GbE MTP To LC Cassette - C-type Labeling |
| ▪ Min. Order UOM | PC |
| ▪ Min. Order Qty. | 1 |
| ▪ BOM Qty. (# of Pkgs.) | <input type="text" value="0"/> |
| ▪ Add to Favorite Product List | <input type="checkbox"/> |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.