

Search Results

- Evaluate
 - FAQ's
 - Performance Data
 - PDF-ETLTest Cert ..
 - PDF-ETLTest Cert ..
 - PDF-ETLTest Cert ..
- Design a Solution
 - Part Drawings
 - PDF-NetKey Cat 6 ..
 - Specification Sheets
 - PDF-NetKey Categ ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'NK6PC14RDY'

Your search criteria matched only one product, shown below

NK6PC14RDY



- Meets Category 6 performance requirements
- Tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Constructed of enhanced performance 24 AWG stranded UTP cable
- 100% performance tested

▪ Part Number	NK6PC14RDY
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Category 6, UTP patch cord with modular plugs on each end.
▪ Product Type	Copper Patch Cord
▪ Color	Red
▪ Length (ft.)	14
▪ Length (m)	4.27
▪ BMEcat - Cable color	Red
▪ Boot Color	Clear
▪ Cable Color	Red
▪ Cable Type	U/UTP
▪ CE Compliant	No
▪ Connector 1 Type	RJ45 8(8)
▪ Connector 2 Type	RJ45 8(8)
▪ Flammability Rating	CM
▪ Performance Level	Category 6/Class E
▪ Pricing Description	NK Copper Patch Cord, Category 6, Red UTP Cable, 14 Feet
▪ Termination End 1	Modular Plug
▪ Termination End 2	Modular Plug
▪ Wiring Scheme	T568B
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.