

Search within category **GO**

**BUY NOW**

**DESIGN / INSTALL**



**QPPN6BU**

QuickNet Plug Pack accepts six Panduit RJ45 modular plugs, Blue.

<span>Specs</span> <span>Packaging Details</span> <span>Documents</span>		<span>★ Add to Favorites</span> <span>🛒 Add to BOM</span>
Color	Blue	
AWG Size	—	
Boot Color	No Boot	
Conductor Material	Copper	
Depth (In.)	2.65	
Depth (mm)	67.31	
Height (In.)	1.67	
Height (mm)	42.42	
Length (ft.)	—	
Model (Design)	Snap-in	
Operating Temperature	14°F to 140°F (-10°C to 60°C)	
Plug Type	6 Pack	
Termination End 1	Modular Plug	
Termination End 2	—	
Used with Installation Tool	No	
RoHS Compliancy Status	Compliant	
Min. Order Qty.	1	