

Search within category **GO**

BUY NOW

DESIGN / INSTALL



GACB-2

Auxiliary cable bracket, 1.63" (41.4mm) width, 3.95" (100.3mm) height, 5.22" (132.6mm) depth, provided with one mounting screw.

Specs **Packaging Details** **Documents** [★ Add to Favorites](#) [Add to BOM](#)

<p>NCG Print Part Description</p>	<p>Supports grounding conductors positioned below Wyr-Grid™ Pathways and automatically makes bonding connection. Used with ladder rack and wire basket.</p>
<p>CSA Certified</p>	<p>CSA 22.2 No.41-13</p>
<p>Mounting Method</p>	<p>Above or Below Pathway</p>
<p>UL Listed</p>	<p>UL 467</p>
<p>Depth (In.)</p>	<p>3.71</p>
<p>Depth (mm)</p>	<p>94.2</p>
<p>Height (In.)</p>	<p>4.18</p>
<p>Height (mm)</p>	<p>106.1</p>
<p>Width (In.)</p>	<p>1.63</p>
<p>Width (mm)</p>	<p>41.4</p>
<p>Material</p>	<p>Zinc Plated Steel</p>
<p>Bonds Ladder Rack Rail Sizes</p>	<p>1 " and 2" Ladder rack rails</p>
<p>Bracket Bonding Feature</p>	<p>Paint Piercing teeth</p>
<p>Compatibility</p>	<p>Wyr-grid & 1 1/2" & 2" Side channel Ladder Rack</p>
<p>For Use With</p>	<p>Wyr-grid & 1 1/2" & 2" Side channel Ladder Rack</p>
<p>Conductor Capacity</p>	<p>up to 4</p>
<p>Max Conductor Size</p>	<p>750 kcmil</p>
<p>Options</p>	<p>Front and Back Mounting Screw Options</p>
<p>Standards</p>	<p>Meets TIA-607-B</p>
<p>Includes</p>	<p>One Mounting Screw</p>
<p>RoHS Compliancy Status</p>	<p>Compliant</p>
<p>Min. Order Qty.</p>	<p>1</p>