



Search within category GO

CLT188N-3C630

Corrugated loom tubing slit wall, 1.88" (47.8mm) x 300' (91.4m), heat stabilized black nylon 6.



BUY NOW

DESIGN / INSTALL

Specs Packaging Details Documents [★ Add to Favorites](#) [Add to BOM](#)

Material	Nylon 6
Color	Black
Flammability Rating	HB
Temperature Range	-40°F - 230°F (-40°C - 110°C)
Length Per Reel (ft.)	300
Length Per Reel (m)	91.4
Inside Diameter (In.)	1.88
Inside Diameter (mm)	47.8
Outside Diameter (In.)	2.17
Outside Diameter (mm)	55.1
Application	Indoor Use
Part Features	Provides protection for cables. Slitted for easier install onto a bundle of wires or a pre-assembled harness assembly
RoHS Compliancy Status	Compliant
Min. Order Qty.	1