

Search Results

- Evaluate
  - FAQ's
  - Product Bulletins
  - PDFCONTOURTY C
- Design a Solution
  - Part Drawings
  - PDFContour Ty C ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'CBR2M-M7'

Your search criteria matched only one product, shown below

### CBR2M-M7



- For indoor use
- Unique design prevents wire and cable damage
- Low profile head avoids snags and reduces overall bundle size
- Outside teeth and smooth round edges protect cable jacket – ideal for high vibration applications
- Parallel-entry limits exposure to sharp edges and protects workers' arms/hands
- Fully enclosed head for consistent strength
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

|                                   |   |
|-----------------------------------|---|
| Part Number                       | CBR2MM7   |
| RoHS Compliancy Status            | Compliant   |
| Part Description                  | Contour-Ty® Cable Tie, ParallelEntry, 7.2", Miniature cross section                   |
| Product Type                      | Cable Ties  |
| Material                          | Nylon 6.6   |
| Color                             | Purple  |
| CSA Certified                     | Yes   |
| Mil. Std. Part Number             | MS3367-32-7   |
| UL Listed (File #E56854)          | Yes   |
| UL Recognized (File #E56854)      | Yes   |
| Length (In.)                      | 7.2   |
| Length (mm)                       | 183   |
| Width (In.)                       | .098  |
| Width (mm)                        | 2.5   |
| CE Compliant                      | Yes   |
| Cross Section                     | Miniature   |
| Head Height (In.)                 | .208  |
| Head Height (mm)                  | 5.3   |
| Head Width (In.)                  | .209  |
| Head Width (mm)                   | 5.3   |
| Locking Style                     | Locking   |
| Material Flammability Rating      | UL 94V-2  |
| Max. Bundle Diameter (In.)        | 2.00  |
| Max. Bundle Diameter (mm)         | 51  |
| Max. Continuous Use Temperature   | 185°F (85°C)  |
| Min. Loop Tensile Strength (Lbs.) | 18  |
| Min. Loop Tensile Strength (N)    | 80  |
| Pricing Description               | Cable Tie, InLine, 7.2"L (183mm), Miniature, Nylon, Purple                            |
| Thickness (In.)                   | .042  |
| Thickness (mm)                    | 1.1   |
| Tool                              | GTS, GTSL, GS2B, PTS, PPTS, STS2  |
| Min. Order UOM                    | PC  |
| Min. Order Qty.                   | 1000  |
| BOM Qty. (# of Pkgs.)             | <input type="text" value="0"/>  |
| Add to Favorite Product List      |  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.