

Search Results

- Evaluate
 - FAQ's
 - Product Bulletins
 - PDFCONTOURTY C
- Design a Solution
 - Part Drawings
 - PDFContour Ty C ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'CBR3IM8'

Your search criteria matched only one product, shown below

CBR3IM8



- For indoor use
- Unique design prevents wire and cable damage
- Low profile head avoids snags and reduces overall bundle size
- Outside teeth and smooth round edges protect cable jacket – ideal for high vibration applications
- Parallel-entry limits exposure to sharp edges and protects workers' arms/hands
- Fully enclosed head for consistent strength
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

Part Number	CBR3IM8
RoHS Compliancy Status	Compliant
Part Description	Contour-Ty® Cable Tie, ParallelEntry, 10.4", Intermediate cross section
Product Type	Cable Ties
Material	Nylon 6.6
Color	Gray
CSA Certified	Yes
Mil. Std. Part Number	MS3367-34-8
UL Listed (File #E56854)	Yes
UL Recognized (File #E56854)	Yes
Length (In.)	10.4
Length (mm)	264
Width (In.)	.140
Width (mm)	3.6
CE Compliant	Yes
Cross Section	Intermediate
Head Height (In.)	.250
Head Height (mm)	6.4
Head Width (In.)	.262
Head Width (mm)	6.7
Locking Style	Locking
Material Flammability Rating	UL 94V-2
Max. Bundle Diameter (In.)	3.00
Max. Bundle Diameter (mm)	76
Max. Continuous Use Temperature	185°F (85°C)
Min. Loop Tensile Strength (Lbs.)	40
Min. Loop Tensile Strength (N)	178
Pricing Description	Cable Tie, InLine, 10.4"L (264mm), Intermediate, Nylon, Gray
Thickness (In.)	.052
Thickness (mm)	1.3
Tool	GTS, GTSL, GS2B, PTS, PPTS, STS2
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.