

Products

Products Overview

Product Search

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- DWG-NETACCESS C ..

- PDFNETACCESS C ..

- DXF-NETACCESS C ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Install & Maintain

- Installation Instructions

- PDFNet-Access C ..

- PDFNet-Access C ..

Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips  Within Results

Part Number > CN2CN

Your search criteria matched only one product, shown below


CN2CN



Net-Access™ Switch Cabinets

- Inset frame posts creating large and accessible vertical pathways for routing cables
- Modular cable management fingers easily mount to the front and/or back of all four cabinet posts
- Designed with the use of CFD (Computational Fluid Dynamics) analysis and thermal lab testing to optimize the thermal performance of network switches requiring side-to-side airflow
- Innovative, fully integrated, electrically bonded cabinet with a single ground connection to guard against EMI and ESD, and provide a safe current path to ground
- Accommodates equipment mounting depths up to 25.9" (658mm)
- Four adjustable equipment mounting rails – available in cage nut or #12 -24 threaded with printed rack space identification
- Doors include keyed swing handles
- Side panels include keyed pushbutton latches
- Durable black polyester epoxy powder coat finish

- 2500 lbs. (1134 kg) load rating
- Cabinet ships assembled, one per pallet
- For the complete grounding solution, see the *StructuredGround™* Kits for Cabinets.
- Designed specifically for use with Net-Access™ Switch and Server Cabinets

Part Number	CN2CN
RoHS Compliancy Status	Compliant
Part Description	Cabinet frame with top panel. Cage nut rails (1224). Dual hinge perforated front door opens to the left or right. Split perforated rear doors open in the middle to minimize door swing footprint. Solid side panels. Two sets of #12 -24 threaded equipment mounting rails. 45 RU cable management on front and rear of front posts. Dimensions: 84.0"H x 31.5"W x 41.0"D (2134mm x 800mm x 1044mm)
Color	Black
No. of Rack Spaces	45
Pricing Description	Network Cabinet With Doors, 45 RU, Cage Nut Rails
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.