

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFMetric Femal ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'DMNF2485FIB-3K'


Your search criteria matched only one product, shown below

DMNF2-485FIB-3K



Standard nylon provides an insulation support for normal requirements. The fully Insulated design gives excellent flashover protection and the funnel entry speeds wire insertion for increased productivity.

- Continuously molded design provides reliable, consistent performance through the applicator for a high quality termination every time
- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
- Fully insulated design provides protection from electrical shorts
- Disconnects available in common industry tab sizes
- Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection

Part Number	DMNF2485FIB-3K
RoHS Compliancy Status	Compliant
Part Description	Metric reel-fed female disconnect, 1.5 - 2.5mm ² wire range, 4.8mm x .5mm tab size, nylon fully insulated, funnel entry.
Product Type	Disconnects – Metric ReelFed
CSA Certified	Yes
UL Listed	Yes
Height (mm)	4.6
Length (mm)	19.8
Width (mm)	7.4
CA-800 Series Crimp Die	CD-800-5
CA9 Series Crimp Die	CD9-5A
Max. Ins.	4.0
Panduit Color Code	Blue
Pieces Per Reel	3000
Pricing Description	Metric Female Disconnect, nylon fully insulated, 1.5- 2.5mm ² wire range, 4.8 x .5mm tab size, funnel entry
Tab Size (mm)	4.8 x .5
Wire Range (mm ²)	1.5 – 2.5
Min. Order UOM	PC
Min. Order Qty.	3000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.