

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'FMDJW24'

Your search criteria matched only one product, shown below

**FMDJW24**



- Mount to standard EIA 19" rack rails
- Standard front or angled front options
- Use with CFAPPBL panels to protect fibers and terminations
- Can be used as a back box for select *Mini-Com*® Patch Panels
- Removable top cover provides access to connections, fibers, and slack storage in rear of tray
- Multiple trunk cable entry locations provided on rear and sides of enclosure
- Include fiber optic cable routing kit (grommets, cable ties, spools, strain relief bracket and ID/caution labels) for various cable management solutions

Part Number	FMDJW24
RoHS Compliancy Status	Compliant
Part Description	Slide out draw er accepts up to 4 FAP or FMP Modular Panels. Rear of tray has pass through holes for rear cable entry. Dimensions: 1.69H (43mm) X 18.27W (464mm) X 11.18D (284mm)
Product Type	Fiber Optic Draw ers
Depth (In.)	11.18
Depth (mm)	284
Height (In.)	1.69
Height (mm)	43
Width (In.)	18.27
Width (mm)	464
No. of Ports	24
No. of Rack Spaces	1
Pricing Description	Rack Mount Fiber Draw er 24 Port (For Japan Only)
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.