

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'HSTT400-48-2'


Your search criteria matched only one product, shown below

HSTT400-48-2



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
 - Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
- For clear, add "C" to end of part number package suffix (Example HSTT05 -48-QC). Contact customer service for additional color information.

Meets Mil Spec AMSDTL-23053/5 Class 1 (Colors), Class 2 (Clear)

▪ Part Number	HSTT40048-2
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Thin Wall Polyolefin Heat Shrink
▪ Material	Flame retardant polyolefin cross-linked except clear
▪ Color	Black†
▪ CSA Certified	Yes
▪ Military Specification	AMS-DTL-23053/5 Class 1
▪ UL Recognized	E122770
▪ Length (ft.)	4
▪ Length (m)	1.2
▪ Flammability Rating	Flame Retardant
▪ Max. Recovered I.D. (In.)	2.00
▪ Max. Recovered I.D. (mm)	50.8
▪ Min. Expanded I.D. (In.)	4.00
▪ Min. Expanded I.D. (mm)	101.6
▪ Nominal Diameter / Size	4.00
▪ Nominal Recovered Wall Thickness (In.)	.055
▪ Nominal Recovered Wall Thickness (mm)	1.4
▪ Pricing Description	Heat Shrink Thin, 4"(101.6mm) Dia, Black
▪ Shrink Ratio	2:1
▪ Temperature Range	-67°F to 275°F (-55°C to 135°C)
▪ Min. Order UOM	PC
▪ Min. Order Qty.	2
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.