

Search Results

- Evaluate
- FAQ's
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'HSTT400-L'

Your search criteria matched only one product, shown below

HSTT400-L



Flexible Polyolefin DRY-SHRINK™ Heat Shrink Tubing

- General Purpose heat shrink tubing for dry locations
- Applications include insulating, protecting, harnessing and identifying wires.
- Material Type: Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 275°F (-55°C to 135°C)
- Flammability Rating: Flame retardant EXCEPT clear
- Voltage: 600 V
- UL Recognized, CSA Certified
- Mil Spec: AMS-DTL-23053/5 Class 1 (Colors) Class 2 (Clear)

▪ Part Number	HSTT400L
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Thin Wall Polyolefin Heat Shrink
▪ Material	Polyolefin cross-linked
▪ Color	Black
▪ CSA Certified	Yes
▪ Military Specification	AMS-DTL-23053/5 Class 1
▪ UL Recognized	E122770
▪ Flammability Rating	Flame Retardant
▪ Length Per Reel (ft.)	50
▪ Length Per Reel (m)	15.2
▪ Max. Recovered I.D. (In.)	2.00
▪ Max. Recovered I.D. (mm)	50.8
▪ Min. Expanded I.D. (In.)	4.00
▪ Min. Expanded I.D. (mm)	101.6
▪ Nominal Diameter / Size	4.00
▪ Nominal Recovered Wall Thickness (In.)	.055
▪ Nominal Recovered Wall Thickness (mm)	1.4
▪ Pricing Description	Heat Shrink Thin, 4"(101.6mm) Dia, Black
▪ Shrink Ratio	2:1
▪ Temperature Range	-67°F to 275°F (-55°C to 135°C)
▪ Min. Order UOM	RL
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.