

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'HSTTPN50-CC'

Your search criteria matched only one product, shown below

HSTTPN50-CC



- Low shrink temperature (store below 90° F) to speed installation
 - Crystal clear material ensures easy to read labels and splice inspections
 - Highly flame retardant product manufactured from a material that is rated UL224 VW -1
 - Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Meets Mil Spec AMS-DTL-23053/2 Class 2.

▪ Part Number	HSTTPN50CC
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Crystal Clear PVC Heat Shrink
▪ Material	Highly flame retardant non cross-linked PVC*
▪ Color	Clear
▪ Military Specification	AMS-DTL-23053/2 Class 2
▪ Continuous Use Temperature Range	-31°F to 221°F (-35°C to 105°C)
▪ Length Per Reel (ft.)	100
▪ Length Per Reel (m)	30.5
▪ Max. Recovered I.D. (In.)	.25
▪ Max. Recovered I.D. (mm)	6.4
▪ Min. Expanded I.D. (In.)	.50
▪ Min. Expanded I.D. (mm)	12.7
▪ Nominal Diameter (In.)	1/2
▪ Nominal Diameter (mm)	12.7
▪ Nominal I.D. (In.)	.50
▪ Nominal I.D. (mm)	12.7
▪ Nominal Recovered Wall Thickness (In.)	.03
▪ Nominal Recovered Wall Thickness (mm)	0.8
▪ Pricing Description	.50" (12.7mm) PVC Heat Shrink Clear
▪ Temperature Range	-31°F to 221°F (-35°C to 105°C)
▪ Min. Order UOM	RL
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.