


Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'HSTTPN62-CC'

Your search criteria matched only one product, shown below

HSTTPN62-CC



- Low shrink temperature (store below 90° F) to speed installation
 - Crystal clear material ensures easy to read labels and splice inspections
 - Highly flame retardant product manufactured from a material that is rated UL224 VW -1
 - Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Meets Mil Spec AMS-DTL-23053/2 Class 2.

Part Number	HSTTPN62CC
RoHS Compliancy Status	Compliant
Part Description	Crystal Clear PVC Heat Shrink
Material	Highly flame retardant non cross-linked PVC*
Color	Clear
Military Specification	AMS-DTL-23053/2 Class 2
Continuous Use Temperature Range	-31°F to 221°F (-35°C to 105°C)
Length Per Reel (ft.)	100
Length Per Reel (m)	30.5
Max. Recovered I.D. (In.)	.31
Max. Recovered I.D. (mm)	7.9
Min. Expanded I.D. (In.)	.63
Min. Expanded I.D. (mm)	15.9
Nominal Diameter (In.)	5/8
Nominal Diameter (mm)	15.9
Nominal I.D. (In.)	.63
Nominal I.D. (mm)	15.9
Nominal Recovered Wall Thickness (In.)	.04
Nominal Recovered Wall Thickness (mm)	1.0
Pricing Description	.63" (15.8mm) PVC Heat Shrink Clear
Temperature Range	-31°F to 221°F (-35°C to 105°C)
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.